

**Garant**
**Die, M: M14**


## Order data

Order number	140400 M14
GTIN	4045197083562
Item class	11K

## Description

### Version:

Closed, pre-slit form. **≥ M3 with tapered lead chamfer** on both sides for easy start to the threading action and clean swarf evacuation in the direction of cutting. **2 turns lead chamfer.**

**Lapped and nitrided**, rake approx. 15°.

Cutting direction: right-hand

Tolerance class: DIN 13 6g

Pitch: 2 mm

External Ø: 38 mm

Height: 14 mm

## Technical description

Pitch	2 mm
Height	14 mm
External Ø	38 mm
Tolerance class	DIN 13 6g

Thread size	M14
Thread type	M
Flank angle	60°
Tool material	HSS E
Standard	EN 22568
Cutting direction	right-hand
Type of product	Die

### User data

	Suitability	V <sub>c</sub>	ISO code
Steel < 500 N/mm <sup>2</sup>	suitable		
Steel < 750 N/mm <sup>2</sup>	suitable		
Steel < 900 N/mm <sup>2</sup>	suitable		
Steel < 1100 N/mm <sup>2</sup>	suitable		
Steel < 1400 N/mm <sup>2</sup>	suitable only under restricted conditions		
INOX < 900 N/mm <sup>2</sup>	suitable		
INOX > 900 N/mm <sup>2</sup>	suitable only under restricted conditions		
Oil	suitable		
dry	suitable only under restricted conditions		