

HOLEX®
Die 6g, M: M16

Order data

Order number	140320 M16
GTIN	4045197083333
Item class	12K

Description
Version:

Closed, pre-slit form. \geq **M3 with tapered lead chamfer** on both sides for easy start to the threading action and clean swarf evacuation in the direction of cutting. **1 3/4 turns lead chamfer.**

Thread type: M

Flank angle: 60 degrees

Tool material: HSS

Norm: EN 22568

Tolerance class: DIN 13 6g

Pitch: 2 mm

External \varnothing : 45 mm

Height: 18 mm

Technical description

Height	18 mm
Pitch	2 mm
External \varnothing	45 mm

Tolerance class	DIN 13 6g
Thread size	16
Thread type	M
Flank angle	60 degrees
Tool material	HSS
Norm	EN 22568
Cutting direction	right-hand