



Pneumatic die grinder, Type: 52862



Order data

Order number	079441 52862
GTIN	616026528628
Item class	03R

Description

Version:

Dynabrade – pneumatic straight die grinder.

Versatile, smooth running straight die grinders of robust and ergonomic design, with soft grip. Well-balanced, slow running small straight grinder with an **adjustable speed up to 25,000 rpm.**

Supplied with:

Including the necessary coupling adaptors.

Technical description

Length	144 mm
Manufacturer's designation	52862
Output power	298 W
maximum speed	25000 min ⁻¹
maximum vibration to EN	2.6 m/s ²
Weight	0.48 kg
Operating noise	79 dB(A)
maximum air consumption	564 l/min
Collet Ø	3 mm
Compressed air connection	1/4 in

Connection thread	NPT
Type of product	Straight die grinder