

HOLEX®
Die, M: M12


Order data

| | |
|--------------|---------------|
| Order number | 140450 M12 |
| GTIN | 4045197595225 |
| Item class | 12K |

Description

Version:

Closed, pre-slit form. **≥ M3 with tapered lead chamfer** on both sides for easy start to the threading action and clean swarf evacuation in the direction of cutting. **2 turns lead chamfer.**

Lapped and nitrided, rake approx. 15°.

Thread type: M

Flank angle: 60 degrees

Tool material: HSS E

Norm: EN 22568

Tolerance class: DIN 13 6g

Pitch: 1.75 mm

External Ø: 38 mm

Height: 14 mm

Technical description

| | |
|------------|---------|
| Height | 14 mm |
| Pitch | 1.75 mm |
| External Ø | 38 mm |

| | |
|-------------------|------------|
| Tolerance class | DIN 13 6g |
| Thread size | 12 |
| Thread type | M |
| Flank angle | 60 degrees |
| Tool material | HSS E |
| Norm | EN 22568 |
| Cutting direction | right-hand |