

Garant**Die 6e, M: M10****Order data**

Order number	140350 M10
GTIN	4045197083401
Item class	11K

Description**Version:**

Closed, pre-slit form. \geq **M3 with tapered lead chamfer** on both sides for easy start to the threading action and clean swarf evacuation in the direction of cutting. **1 $\frac{3}{4}$ turns lead chamfer**. Tolerance zone 6e = **with undersize approx. 0.03 – 0.04 mm**. For tolerance class "medium", when studs are provided with a **galvanic protection coating**.

Technical description

Pitch	1.5 mm
Height	11 mm
External \varnothing	30 mm
Tolerance class	DIN 13 6g
Thread size	M10
Thread type	M
Flank angle	60 degrees

Tool material	HSS
Standard	EN 22568
Cutting direction	right-hand
Type of product	Die

User data

	Suitability	V_c	ISO code
Aluminium (short chipping)	suitable only under restricted conditions		
Steel < 500 N/mm ²	suitable		
Steel < 750 N/mm ²	suitable		
Oil	suitable		
dry	suitable only under restricted conditions		