

HOLEX®
Die 6g, M: M10

Order data

Order number	140320 M10
GTIN	4045197083302
Item class	12K

Description
Version:

Closed, pre-slit form. \geq **M3 with tapered lead chamfer** on both sides for easy start to the threading action and clean swarf evacuation in the direction of cutting. **1 3/4 turns lead chamfer.**

Thread type: M

Flank angle: 60 degrees

Tool material: HSS

Norm: EN 22568

Tolerance class: DIN 13 6g

Pitch: 1.5 mm

External \varnothing : 30 mm

Height: 11 mm

Technical description

Height	11 mm
Pitch	1.5 mm
External \varnothing	30 mm

Tolerance class	DIN 13 6g
Thread size	10
Thread type	M
Flank angle	60 degrees
Tool material	HSS
Norm	EN 22568
Cutting direction	right-hand