

HOLEX®
Die, M: M5


Order data

Order number	140450 M5
GTIN	4045197595171
Item class	12K

Description

Version:

Closed, pre-slit form. \geq **M3 with tapered lead chamfer** on both sides for easy start to the threading action and clean swarf evacuation in the direction of cutting. **2 turns lead chamfer.**

Lapped and nitrided, rake approx. 15°.

Thread type: M

Flank angle: 60 degrees

Tool material: HSS E

Norm: EN 22568

Tolerance class: DIN 13 6g

Pitch: 0.8 mm

External \varnothing : 20 mm

Height: 7 mm

Technical description

Pitch	0.8 mm
Height	7 mm
External \varnothing	20 mm

Tolerance class	DIN 13 6g
Thread size	5
Thread type	M
Flank angle	60 degrees
Tool material	HSS E
Norm	EN 22568
Cutting direction	right-hand