

Garant
Hand tap set, uncoated, M: M27

Order data

Order number	130150 M27
GTIN	4045197065490
Item class	11G

Description
Version:

Set of three, **consisting of taper, second, and plug tap.**

Size M2.3 and M2.6 to old DIN profile.

Thread type: M

Tool material: HSS

Standard: DIN 352

Tolerance class: ISO 2 6H

Thread pitch: 3 mm

Overall length L: 110 mm

Shank \varnothing D_s: 20 mm

Shank square □: 16 mm

Tapping hole \varnothing : 24 mm

Technical description

Tapping hole \varnothing	24 mm
Thread \varnothing	27 mm
Thread pitch	3 mm
Standard	DIN 352

Shank $\varnothing D_s$	20 mm
Overall length L	110 mm
Shank square \square	16 mm
Tolerance class	ISO 2 6H
Tool material	HSS
Thread depth	54 mm
Thread type	M
Thread size	M27
Coating	uncoated
Flank angle	60°
Thread standard	DIN 13
Taper lead form	A
Taper lead form	D
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for blind holes
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Hand tap
Colour ring	without
Type of product	Tap

User data

	Suitability	V_c	ISO code
Alu plastics	suitable only under restricted conditions		
Aluminium (short chipping)	suitable only under restricted conditions		

Alu > 10% Si	suitable only under restricted conditions
Steel < 500 N/mm ²	suitable
Steel < 750 N/mm ²	suitable
Steel < 900 N/mm ²	suitable
GG(G)	suitable only under restricted conditions
Uni	suitable only under restricted conditions
Oil	suitable
dry	suitable only under restricted conditions