

**Multi-purpose oil, Type: 5000****Order data**

Order number	083005 5000
GTIN	5032227495005
Item class	08E

**Description****Version:**

WD-40 multi-function oil is proven world-wide, **almost completely odourless, uses non-polluting propellant**, is Teflon, resin, silicone, and acid-free.

**Application:**

- **Rust remover with penetrating capillary action – quickly releases seized bolts and nuts.**
- **Cleaner – loosens stubborn dirt, without sticking or gumming up.**
- **Lubricant for all sliding surfaces, precision mechanics, hinges, Bowden cables, locks and catches.**
- **Corrosion protection – WD-40 penetrates under moisture and into the pores of the material to be protected, thus preserving it. Delicate and expensive tools retain their value.**
- **Contact spray – displaces moisture from electrical components.**

By wide-scale use **of the spray dispenser No. 083006 or No. 083509 – 083517** for economic application over large surfaces.

**Note:**

Approved by: **Rolls Royce, Daimler, Airbus, VW** amongst others.

Not available in all countries. Express delivery not possible.

**Technical description**

Kinematic viscosity	< 1 mm <sup>2</sup> /s
Solubility in water	insoluble
Flashpoint	47 °C
Labelling of hazardous substances	GHS08 harmful to health
Labelling of hazardous substances	GHS07 caution
Labelling of hazardous substances	GHS02: Flame
Colour	amber colours
Oxidisation characteristics	not suitable
Boiling point	176 °C
Contents	5 l
Version	Can
Type of product	Multi-function oil / universal oil