

SONO+SWISS®

Ultrasonic power cleaner T4, Capacity l/kg: 10**Order data**

Order number	082934 10
GTIN	2050002050358
Item class	04E

Description**Version:**

High-yield water-based cleaning concentrate (exception: T3 supplied in powdered form); specially developed for use in ultrasonic cleaning baths; biologically degradable. The high-yielding **concentrates** extend the working life of the devices, last a long time, and are biologically degradable. The power cleaners have been specially developed for ultrasonic baths (foaming characteristics etc.) and are therefore particularly effective for all conventional ultrasonic cleaning baths operating at frequencies in the range 25 to 130 kHz. In conjunction with the cavitation forces created by the ultrasonic vibration the power cleaner releases the dirt gently but effectively whilst treating the components gently. Other cleaning agents which have not been developed specially for ultrasonic baths may under certain circumstances promote corrosion or removal of material. Halogen ions are an example of aggressive corrosion promoters which greatly reduce the working life. Chlorides and fluorides in acid media are the most aggressive in this respect.

Application:

For ultrasonic cleaning baths (such as No. 082922; 082923; 082924; 082925).

Note:

Other special cleaners and other container sizes available on request. 25-litre drums are available in the online shop.

Unavailable in some countries.

Technical description

Type of cleaning agent	Neutral cleaner
Processing time	1 - 5 min
Manufacturer's designation	T4
Mixing ratio	5 – 10 %
Storage temperature	5 - 30 °C
Fill capacity liquid	10 l
Type of product	Ultrasonic power cleaner