

Garant
Heavy-Duty-Plus blade carrier for face grooving, left-hand, Ø range Groove D1 / D2: 234/350mm

Order data

Order number	274082 234/350
GTIN	4062406378660
Item class	21U

Description
Version:

For grooving inserts No. 275021 – 275048.

Application:

In conjunction with toolholder No. 274006.

Attention:

Without clamping screws (these are supplied with the toolholders). Please order the assembly key No. 279940 separately.

Note:

D_1 = minimum Ø for the first groove / D_2 = maximum Ø for the first cut.

$D_2 = 999$ in the size designation corresponds to theoretically infinite.

Technical description

minimum 1st groove Ø D_1	234 mm
maximum cutting depth t_{max}	120 mm
maximum 1st groove Ø D_2	350 mm
Application type	left-hand
System key	yes
Groove width w	8 mm
Type of product	Cartridges

