

**HOLEX®**
**Die HSS-E, M× pitch: 16X1**

**Order data**

Order number	141065 16X1
GTIN	4045197595379
Item class	12K

**Description**
**Version:**

Closed, pre-slit form, **with tapered lead chamfer on both sides.**

**2 turns lead chamfer. Lapped and nitrided, rake approx. 15°. For stainless and high-tensile steels.**

Thread type: MF

Flank angle: 60 degrees

Tool material: HSS E

Norm: EN 22568

Tolerance class: DIN 13 6g

Pitch: 1 mm

External Ø: 45 mm

Height: 14 mm

**Technical description**

Pitch	1 mm
Height	14 mm
External Ø	45 mm

Tolerance class	DIN 13 6g
Thread size	16
Thread type	MF
Flank angle	60 degrees
Tool material	HSS E
Norm	EN 22568
Cutting direction	right-hand