

HOLEX®
Die HSS, M× pitch: 12X1,5

Order data

Order number	141060 12X1,5
GTIN	4045197084378
Item class	12K

Description
Version:

Closed, pre-slit form, **with tapered lead chamfer on both sides.**

1¾ turns lead chamfer.

Thread type: MF

Flank angle: 60 degrees

Tool material: HSS

Norm: EN 22568

Tolerance class: DIN 13 6g

Pitch: 1.5 mm

External Ø: 38 mm

Height: 10 mm

Technical description

Pitch	1.5 mm
Height	10 mm
External Ø	38 mm

Tolerance class	DIN 13 6g
Thread size	12
Thread type	MF
Flank angle	60 degrees
Tool material	HSS
Norm	EN 22568
Cutting direction	right-hand