

HOLEX®
Die HSS-E, M× pitch: 10X1,25


Order data

Order number	141065 10X1,25
GTIN	4045197595317
Item class	12K

Description

Version:

Closed, pre-slit form, **with tapered lead chamfer on both sides.**

2 turns lead chamfer. Lapped and nitrided, rake approx. 15°. For stainless and high-tensile steels.

Thread type: MF

Flank angle: 60 degrees

Tool material: HSS E

Norm: EN 22568

Tolerance class: DIN 13 6g

Pitch: 1.25 mm

External Ø: 30 mm

Height: 11 mm

Technical description

Pitch	1.25 mm
Height	11 mm
External Ø	30 mm

Tolerance class	DIN 13 6g
Thread size	10
Thread type	MF
Flank angle	60 degrees
Tool material	HSS E
Norm	EN 22568
Cutting direction	right-hand