

**HOLEX®****Die HSS, M× pitch: 14X1,5****Order data**

Order number	141060 14X1,5
GTIN	4045197084385
Item class	12K

**Description****Version:**Closed, pre-slit form, **with tapered lead chamfer on both sides.****1¾ turns lead chamfer.**

Thread type: MF

Flank angle: 60 degrees

Tool material: HSS

Norm: EN 22568

Tolerance class: DIN 13 6g

Pitch: 1.5 mm

External Ø: 38 mm

Height: 10 mm

**Technical description**

Height	10 mm
Pitch	1.5 mm
External Ø	38 mm

Tolerance class	DIN 13 6g
Thread size	14
Thread type	MF
Flank angle	60 degrees
Tool material	HSS
Norm	EN 22568
Cutting direction	right-hand