

Garant
Die Hexagon, M: M5

Order data

Order number	140920 M5
GTIN	4045197083869
Item class	11K

Description
Version:

External hexagon for standard socket size. **Without** tapered spiral point. **1¾ turns lead chamfer.**

Note:

For re-cutting damaged threads or for cutting where access is difficult.

Tolerance class: DIN 13 6g

Pitch: 0.8 mm

Width across flats: 18 mm

Height: 7 mm

Technical description

Pitch	0.8 mm
Height	7 mm
Width across flats	18 mm
Thread size	M5
Thread type	M

Flank angle	60°
Tool material	HSS
Standard	DIN 382
Tolerance class	DIN 13 6g
Type of product	Die

User data

	Suitability	V _c	ISO code
Aluminium (short chipping)	suitable only under restricted conditions		
Steel < 500 N/mm ²	suitable		
Steel < 750 N/mm ²	suitable		
Steel < 900 N/mm ²	suitable		
Steel < 1100 N/mm ²	suitable only under restricted conditions		
INOX < 900 N/mm ²	suitable only under restricted conditions		
CuZn	suitable only under restricted conditions		
Oil	suitable		
dry	suitable only under restricted conditions		