

PRYOR

Numeral letter punch set, 27 pieces Mirror script A – Z, &, Character height: 2mm



Order data

| | |
|--------------|---------------|
| Order number | 085440 2 |
| GTIN | 5022044007574 |
| Item class | 08W |

Description

Version:

Made of hard and tough steel with particularly precise machine engraving and depth tolerance; accurately centred. Calibrated shank, through hardened. Striking head enhancement for safe working. Supplied in a plastic case.

High performance precision punches, chemically nickel-plated, very long service life.

Mirror script; i.e. the punched character appears laterally reversed on the component (for die making).

Application:

For punching into materials with a **strength up to 1200 N/mm²**.

Spare part:

Individual number punches under No. 085411 size font height/number, e. g. No. 085411 size 3/1.

Individual letter punches under No. 085431 size font height/character, e.g. No. 085431 size 3/A.

Note:

Other hand and machine punches of all types, such as punches with a company's logo etc., are available on request.

Technical description

| | |
|------------------|------------|
| overall length | 63.5 mm |
| Shank thickness | 6.35 |
| Character height | 2 mm |
| Type of product | Hand punch |

Accessories

| | |
|------------------------|-------------|
| Punch holder Type GRIP | 085475 GRIP |
|------------------------|-------------|