

**HOLEX®**
**Die HSS-E, M× pitch: 14X1,5**

**Order data**

Order number	141065 14X1,5
GTIN	4045197595362
Item class	12K

**Description**
**Version:**

Closed, pre-slit form, **with tapered lead chamfer on both sides.**

**2 turns lead chamfer. Lapped and nitrided, rake approx. 15°. For stainless and high-tensile steels.**

Thread type: MF

Flank angle: 60 degrees

Tool material: HSS E

Norm: EN 22568

Tolerance class: DIN 13 6g

Pitch: 1.5 mm

External Ø: 38 mm

Height: 10 mm

**Technical description**

Height	10 mm
Pitch	1.5 mm
External Ø	38 mm

Tolerance class	DIN 13 6g
Thread size	14
Thread type	MF
Flank angle	60 degrees
Tool material	HSS E
Norm	EN 22568
Cutting direction	right-hand