

PRYOR

Numeral letter punch set, 27 pieces Mirror script A – Z, &, Character height: 3mm



Order data

Order number	085440 3
GTIN	5022044007604
Item class	08W

Description

Version:

Made of hard and tough steel with particularly precise machine engraving and depth tolerance; accurately centred. Calibrated shank, through hardened. Striking head enhancement for safe working. Supplied in a plastic case.

High performance precision punches, chemically nickel-plated, very long service life.

Mirror script; i.e. the punched character appears laterally reversed on the component (for die making).

Application:

For punching into materials with a **strength up to 1200 N/mm²**.

Spare part:

Individual number punches under No. 085411 size font height/number, e. g. No. 085411 size 3/1.

Individual letter punches under No. 085431 size font height/character, e.g. No. 085431 size 3/A.

Note:

Other hand and machine punches of all types, such as punches with a company's logo etc., are available on request.

Technical description

Shank thickness	6.35
Character height	3 mm
overall length	63.5 mm
Type of product	Hand punch

Accessories

Punch holder Type GRIP	085475 GRIP
------------------------	-------------