

Garant
Die, BSW: W3/16


Order data

Order number	141550 W3/16
GTIN	4045197084460
Item class	11K

Description

Version:

Closed, pre-slit form; **with tapered lead chamfer on both sides** for easy start to the threading action and clean swarf evacuation in the direction of cutting. **1¾ turns lead chamfer.**

Application:

For Whitworth threads to BSW standard BS84 in the tolerance field "medium".

Technical description

Threads per inch	24
Thread Ø	4.76 mm
Height	7 mm
External Ø	20 mm
Thread size	W3/16
Cutting direction	right-hand
Tolerance class	medium

Thread type	BSW
Flank angle	55 degrees
Tool material	HSS
Standard	EN 22568
Type of product	Die

User data

	Suitability	V _c	ISO code
Aluminium (short chipping)	suitable only under restricted conditions		
Steel < 500 N/mm ²	suitable		
Steel < 750 N/mm ²	suitable		
Oil	suitable		
dry	suitable only under restricted conditions		