

Garant**Die, G: G1.1/4**

Order data

Order number	142060 G1.1/4
GTIN	4045197084705
Item class	11K

Description

Version:**Hexagon** die **without** tapered lead chamfer; for re-cutting.**Application:****For Whitworth parallel pipe threads** DIN ISO 228/1

Standard: DIN 382

Threads per inch: 11

Thread Ø: 41.91 mm

Width across flats: 70 mm

Height: 20 mm

Technical description

Height	20 mm
Width across flats	70 mm
Thread Ø	41.91 mm
Threads per inch	11
Thread size	G1.1/4

Tolerance class	A
Cutting direction	right-hand
Thread type	G
Flank angle	55 °
Tool material	HSS
Standard	DIN 382
Type of product	Die

User data

	Suitability	V _c	ISO code
Aluminium (short chipping)	suitable only under restricted conditions		
Steel < 500 N/mm ²	suitable		
Steel < 750 N/mm ²	suitable		
Steel < 900 N/mm ²	suitable		
Steel < 1100 N/mm ²	suitable only under restricted conditions		
INOX < 900 N/mm ²	suitable only under restricted conditions		
CuZn	suitable only under restricted conditions		
Oil	suitable		
dry	suitable only under restricted conditions		