

Garant**Die, G: G3/4**

Order data

| | |
|--------------|---------------|
| Order number | 142050 G3/4 |
| GTIN | 4045197084620 |
| Item class | 11K |

Description

Version:

Closed, pre-slitted form; **with tapered lead chamfer on both sides** for easy start to the threading action and clean swarf evacuation in the direction of cutting. **1 $\frac{3}{4}$ turns lead chamfer.**

Application:

For Whitworth parallel pipe threads DIN ISO 228/1

Standard: EN 24231
Threads per inch: 14
Thread \varnothing : 26.44 mm
External \varnothing : 55 mm
Height: 16 mm

Technical description

| | |
|------------------------|----------|
| Threads per inch | 14 |
| Height | 16 mm |
| Thread \varnothing | 26.44 mm |
| External \varnothing | 55 mm |

| | |
|-------------------|------------|
| Thread size | G3/4 |
| Cutting direction | right-hand |
| Tolerance class | A |
| Thread type | G |
| Flank angle | 55° |
| Tool material | HSS |
| Standard | EN 24231 |
| Type of product | Die |

User data

| | Suitability | V _c | ISO code |
|-------------------------------|---|----------------|----------|
| Aluminium (short chipping) | suitable only under restricted conditions | | |
| Steel < 500 N/mm ² | suitable | | |
| Steel < 750 N/mm ² | suitable | | |
| Oil | suitable | | |
| dry | suitable only under restricted conditions | | |