

Garant
Hand tap set, uncoated, MF: 18X1

Order data

Order number	130470 18X1
GTIN	4045197067111
Item class	11G

Description
Version:

2-piece set **comprising taper and plug tap**. Thread ground with radial thread relief.

Thread type: MF

Tool material: HSS

Standard: DIN 2181

Tolerance class: ISO 2 6H

Thread pitch: 1 mm

Overall length L: 80 mm

Shank $\varnothing D_s$: 14 mm

Shank square \square : 11 mm

Tapping hole \varnothing : 17 mm

Technical description

Tapping hole \varnothing	17 mm
Thread \varnothing	16 mm
Thread pitch	1 mm
Shank $\varnothing D_s$	14 mm
Overall length L	80 mm
Shank square \square	11 mm
Tolerance class	ISO 2 6H

Tool material	HSS
Standard	DIN 2181
Thread depth	36 mm
Thread type	MF
Thread size	M18×1
Coating	uncoated
Flank angle	60°
Thread standard	DIN 13
Taper lead form	C
Taper lead form	D
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for blind holes
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Hand tap
Colour ring	without
Type of product	Tap

User data

	Suitability	V _c	ISO code
Alu plastics	suitable only under restricted conditions		
Aluminium (short chipping)	suitable only under restricted conditions		
Alu > 10% Si	suitable only under restricted conditions		
Steel < 500 N/mm ²	suitable		
Steel < 750 N/mm ²	suitable		
Steel < 900 N/mm ²	suitable		

GG(G)	suitable only under restricted conditions
Uni	Suitable
Oil	suitable
dry	suitable only under restricted conditions