

Garant

Precision countersinks with unequal spacing 90°, TiAlN, External Ø Dc: 6,3 mm



Order data

Order number	150130 6,3
GTIN	4045197700704
Item class	11M

Description

Version:

All countersinks have 3 cutting edges. Special geometry with extremely unequal spacing and matching cutting edge preparation. Radially relief ground. Flutes ground from solid. Newly developed **special TiAlN coating** for long service life.

High-precision countersink, produced with tight manufacturing tolerances similar to DIN 335-C.

Advantage:

Very smooth cutting throughout the entire countersinking operation. Chatter-free running for perfect results and **optimum tool service life**.

Application:

High-precision countersinks for production of exactly round 90° countersunk surfaces.

Through-coolant: no

Number of cutting edges Z: 3

Number of cutting edges Z: 3

smallest countersink Ø for holes from: 1.5 mm

Overall length L: 45 mm

Shank Ø D_s: 5 mm

for countersunk screws DIN 7991: M3

Feed f in steel < 500 N/mm²: 0.1 mm/rev.

Technical description

smallest countersink Ø for holes from	1.5 mm
for countersunk screws DIN 7991	M3

Feed f in steel < 500 N/mm ²	0.1 mm/rev.
External Ø	6.3 mm
Shank tolerance	h9
Shank Ø D _s	5 mm
Overall length L	45 mm
Number of cutting edges Z	3
Coating	TiAlN
Countersink tip angle	90 degrees
Tool material	HSS
Spacing of the countersink cutting edges	unequal spacing
Standard	DIN 335 C
Shank	Plain shank with h9
Through-coolant	no
Colour ring	green
Type of product	Stepped drill and countersink