

**Garant**
**High-precision countersink 90°, TiAlN, External Ø Dc: 6mm**

**Order data**

Order number	150170 6
GTIN	4045197301314
Item class	11M

**Description**
**Version:**

**All countersinks have 3 cutting edges**, radially relieved.

Flutes are ground from solid.

Precision countersink for considerable performance improvement.

**Application:**

High precision countersinks for chatter-free countersinking.

**Technical description**

smallest countersink Ø for holes from	1.5 mm
for countersunk screws ISO 2009, 2010, 7046, 7047	M3
Feed f in steel < 500 N/mm <sup>2</sup>	0.09 mm/rev.
Shank tolerance	h9
External Ø	6 mm
Shank Ø D <sub>s</sub>	5 mm
Overall length L	45 mm
Number of cutting edges Z	3
Coating	TiAlN
Countersink tip angle	90 degrees
Tool material	HSS
Standard	DIN 335 C

Shank	Plain shank with h9
Through-coolant	no
Colour ring	green
Type of product	Stepped drill and countersink

## User data

	Suitability	V <sub>c</sub>	ISO code
Alu > 10% Si	suitable only under restricted conditions	25 m/min	N
Steel < 500 N/mm <sup>2</sup>	suitable	34 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	32 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	32 m/min	P
INOX < 900 N/mm <sup>2</sup>	suitable	9 m/min	M
INOX > 900 N/mm <sup>2</sup>	suitable only under restricted conditions	8 m/min	M
CuZn	suitable only under restricted conditions	80 m/min	N
Uni	suitable		
wet maximum	suitable		
dry	suitable only under restricted conditions		