



## Oil atomiser, Internal thread $\varnothing$ : 3/8in



### Order data

Order number	080013 3/8
GTIN	4047322244794
Item class	08A

### Description

#### Version:

Service units can be made up as required; the connection clip supplied can be used to add extensions.

**Service unit** in modular series ("multifix" system), consisting of filter, pressure regulator and mist atomiser. Control range 0.5- 10 bar, operating pressure maximum 16 bar, operating temperature maximum 60 °C.

#### Advantage:

The service unit can be configured individually, e. g. with several pressure regulators, without oil atomiser (for oil-free tools) etc.

#### Application:

For systems in the pressure range up to 16 bar. Compatible with the products of CEJN, RECTUS and JWL.

### Technical description

Height (H)	196 mm
Internal thread $\varnothing$	3/8 in
Flow rate for 3-part service unit	1150 l/min

Overall length (L) as 3-part service unit	183 mm
Type of product	Oilers

---

## Accessories

Polycarbonate container for oiler Glass Ø 33 mm	080023 33
---	-----------