



Countersink 90°, uncoated, External Ø Dc: 6mm



Order data

Order number	150175 6
GTIN	4045197085702
Item class	12M

Description

Version:

All countersinks have 3 cutting edges, radially relieved.

Flutes are ground from solid.

Economy countersink version.

Application:

High precision countersinks for chatter-free countersinking.

Technical description

for countersunk screws ISO 2009, 2010, 7046, 7047	M3
smallest countersink Ø for holes from	1.5 mm
Shank tolerance	h9
External Ø	6 mm
Feed f in steel < 500 N/mm ²	0.09 mm/rev.
Shank Ø D _s	5 mm
Overall length L	45 mm
Number of cutting edges Z	3
Coating	uncoated
Countersink tip angle	90 degrees
Tool material	HSS

Standard	DIN 335 C
Shank	Plain shank with h9
Through-coolant	no
Colour ring	without
Type of product	Stepped drill and countersink

User data

	Suitability	V _c	ISO code
Alu plastics	suitable	70 m/min	N
Aluminium (short chipping)	suitable	33 m/min	N
Steel < 500 N/mm ²	suitable	28 m/min	P
Steel < 750 N/mm ²	suitable only under restricted conditions	27 m/min	P
Steel < 900 N/mm ²	suitable only under restricted conditions	27 m/min	P
Steel < 1100 N/mm ²	suitable only under restricted conditions	8 m/min	P
wet maximum	suitable		
dry	suitable only under restricted conditions		