

**Pneumatic scriber DynaPen®, Manufacturer's designation: 10851****Order data**

Order number	079708 10851
GTIN	616026108516
Item class	03R

Description**Version:**

DynaPen pencil-sized pneumatic pen with a **comprehensive accessories set (1/8 inch)**. The pulsating drive movement (amplitude 0.018 mm) permits **many applications** such as engraving, lettering, light cleaning, and filing work, as well as deburring etc.

Supplied with:

1.4 m connection hose, 3 files, engraving tip, and a hexagon key.

Note:

See No. 529420 for suitable diamond mini-files.

maximum air consumption: 28.2 l/min

Impact frequency: 233 Hz

Thread of the compressed air connection port: 1/4" NPT inch

Weight: 0.26 kg

Operating noise: 79 dB(A)

maximum vibration to EN: 8 m/s²

Technical description

Warranty period for the machine	a
Type of product	