



Pneumatic belt linisher, Type: G2410



Order data

Order number	079571 G2410
GTIN	7322590038366
Item class	03R

Description

Version:

Atlas Copco belt linishing machine for use in **confined places**. The angle between handle and linishing belt guide can be adjusted for improved handling. Linishing belt dimensions 13×305 mm (see No. 558205, 558423).

Application:

For abrading, deburring, blending, finishing and polishing, ideal also for flexible access to difficult places.

Supplied with:

Including the necessary coupling adaptors.

Spare part:

Selected service kits: Sets of replacement parts for most Atlas Copco pneumatic tools can be supplied on request for preventive maintenance and servicing.

Note:

Other contact arm versions for Dynaflex® from No. 079559 available on request or in our eShop.

Output power: 275 W

maximum speed: 25000 rpm

maximum air consumption: 660 l/min

Connection thread: BSW

Compressed air connection: 1/4 inch

Tape width: 13 mm

Technical description

Band length	305 mm
maximum speed	25000 rpm
maximum vibration to EN	< 2.5 m/s ²
Operating noise	89 dB(A)
Weight	0.9 kg
Tape width	13 mm
Output power	275 W
Manufacturer's designation	G2410
maximum air consumption	660 l/min
Compressed air connection	1/4 inch
Connection thread	BSW
Type of product	Linishing machine

Accessories

Contact arm for belt linisher G2410 Type 2410	079563 2410
---	-------------