

Garant**Countersink set No. 150379 in a case 90°, TiCN, Number of countersinks: 17****Order data**

Order number	150385 17
GTIN	4045197445834
Item class	11M

Description**Version:**

Countersink sets, **in a case.**

Practical set for assembly and workshop use.

All countersinks have 3 cutting edges, radially relieved.

Flutes are ground from solid.

High-precision countersink, produced with tight manufacturing tolerances similar to DIN 335-C.

Content:

1× each precision countersink: Size 4.3; 5; 6; 6.3; 7; 8; 8.3; 10; 10.4; 11.5; 12.4; 15; 16.5; 19; 20.5; 23; 25

Technical description

Number of countersinks	17
Number of cutting edges Z	3
Coating	TiCN
Countersink tip angle	90 degrees

Tool material	HSS E
Standard	DIN 335 C
Shank	Plain shank with h9
Colour ring	blue
Type of product	Stepped drill and countersink

Accessories

High-precision countersink90° External Ø Dc 25 mm	150379 25
High-precision countersink90° External Ø Dc 5 mm	150379 5
High-precision countersink90° External Ø Dc 7 mm	150379 7
High-precision countersink90° External Ø Dc 12,4 mm	150379 12,4
High-precision countersink90° External Ø Dc 11,5 mm	150379 11,5
High-precision countersink90° External Ø Dc 10,4 mm	150379 10,4
High-precision countersink90° External Ø Dc 15 mm	150379 15
High-precision countersink90° External Ø Dc 20,5 mm	150379 20,5
High-precision countersink90° External Ø Dc 6 mm	150379 6
High-precision countersink90° External Ø Dc 8,3 mm	150379 8,3
High-precision countersink90° External Ø Dc 6,3 mm	150379 6,3
High-precision countersink90° External Ø Dc 16,5 mm	150379 16,5
High-precision countersink90° External Ø Dc 4,3 mm	150379 4,3
High-precision countersink90° External Ø Dc 10 mm	150379 10
High-precision countersink90° External Ø Dc 8 mm	150379 8
High-precision countersink90° External Ø Dc 19 mm	150379 19
High-precision countersink90° External Ø Dc 23 mm	150379 23