

## Flat magnet with internal thread, Ferrite, Ø: 20mm



### Order data

Order number	085915 20
GTIN	2050000965265
Item class	08Q

### Description

#### Version:

- **Shielded flat magnet made of hard ferrite with insert nut.**
- **Galvanised surface.**
- **Temperature-resistant up to maximum 120 °C.**

#### Application:

For clamping, assembling, incorporation by screw fastening.

#### Note:

Screw-in hooks with external thread under No. 085921.

### Technical description

Material of the surface	galvanised
Ø	20 mm
maximum temperature resistance	120 °C
Thread	M3 mm
Height	6 mm
Nominal clamping force	30 N
Height with thread	13 mm
Threaded socket	yes
Weight	11 g

Material of the magnet core	Ferrite
Type of product	Flat gripper magnet

---

## Accessories

Screw-in hook set with external thread 10 pieces Thread M3	085921 M3
--	-----------