

Garant**Countersink set No. 150379 in a case 90°, TiCN, Number of countersinks: 7****Order data**

Order number	150385 7
GTIN	4045197445827
Item class	11M

Description**Version:**

Countersink sets, **in a case.**

Practical set for assembly and workshop use.

All countersinks have 3 cutting edges, radially relieved.

Flutes are ground from solid.

High-precision countersink, produced with tight manufacturing tolerances similar to DIN 335-C.

Content:

1× each precision countersink: Size 6; 8; 10; 11.5; 15; 19; 25

Note:

Supplied in a case No. 150370 **size 6.**

Technical description

Number of countersinks	7
Number of cutting edges Z	3
Coating	TiCN
Countersink tip angle	90 degrees

Tool material	HSS E
Standard	DIN 335 C
Shank	Plain shank with h9
Colour ring	blue
Type of product	Stepped drill and countersink

Accessories

High-precision countersink90° External Ø Dc 11,5 mm	150379 11,5
High-precision countersink90° External Ø Dc 25 mm	150379 25
High-precision countersink90° External Ø Dc 8 mm	150379 8
High-precision countersink90° External Ø Dc 6 mm	150379 6
High-precision countersink90° External Ø Dc 15 mm	150379 15
High-precision countersink90° External Ø Dc 19 mm	150379 19
High-precision countersink90° External Ø Dc 10 mm	150379 10