

Flat magnet without thread, Ferrite, Ø: 50mm



Order data

Order number	085910 50
GTIN	2050000965074
Item class	08Q

Description

Version:

Shielded flat magnets with magnetic core made of **hard ferrite**.

- **Galvanised surface.**
- **Temperature-resistant up to maximum 120 °C.**

Application:

For clamping, assembling, incorporation by pressing in / gluing and fixing / holding.

Technical description

Ø	50 mm
maximum temperature resistance	120 °C
Nominal clamping force	220 N
Height	10 mm
Weight	100 g
Material of the magnet core	Ferrite
Type of product	Flat gripper magnet