

Garant
High-precision countersink 90°, uncoated, External Ø Dc: 50mm

Order data

Order number	150390 50
GTIN	4045197086839
Item class	11M

Description
Version:

Countersinks radially relief ground. Chip flutes are ground from solid up to size 31. Chip angle varies with the countersink Ø for optimum chip formation. Countersink point and circumference are relief ground and cut easily.

High-precision countersink, produced with tight manufacturing tolerances similar to DIN 335-D.

Note:

For suitable reducing adapters for tools with MT shanks see **No. 343000-343530**.

For countersink bits with shank 6.3 mm (1/4 inch) see Group 67.

Technical description

External Ø	50 mm
Pre-drill Ø	14 mm
smallest countersink Ø for holes from	14 mm
Feed f in steel < 500 N/mm ²	0.25 mm/rev.
Overall length L	150 mm
Morse taper MT	3
Number of cutting edges Z	3
Coating	uncoated
Countersink tip angle	90 degrees
Tool material	HSS

Standard	DIN 335 D
Shank	Morse taper
Through-coolant	no
Colour ring	without
Type of product	Stepped drill and countersink

User data

	Suitability	V_c	ISO code
Alu plastics	suitable	70 m/min	N
Aluminium (short chipping)	suitable	33 m/min	N
Steel < 500 N/mm ²	suitable	28 m/min	P
Steel < 750 N/mm ²	suitable	27 m/min	P
Steel < 900 N/mm ²	suitable only under restricted conditions	27 m/min	P
wet maximum	suitable		
dry	suitable only under restricted conditions		