

## Flat magnet with internal thread, Ferrite, Ø: 25mm



### Order data

Order number	085915 25
GTIN	2050000965272
Item class	08Q

### Description

#### Version:

- **Shielded flat magnet made of hard ferrite with insert nut.**
- **Galvanised surface.**
- **Temperature-resistant up to maximum 120 °C.**

#### Application:

For clamping, assembling, incorporation by screw fastening.

#### Note:

Screw-in hooks with external thread under No. 085921.

### Technical description

Threaded socket	yes
Nominal clamping force	40 N
Ø	25 mm
Height	7 mm
maximum temperature resistance	120 °C
Height with thread	15 mm
Thread	M4 mm
Material of the surface	galvanised
Weight	22 g

Material of the magnet core	Ferrite
Type of product	Flat gripper magnet

---

## Accessories

Screw-in hook set with external thread 10 pieces Thread M4	085921 M4
--	-----------