

Garant

Power saw blade, HSS, Length L / TPI: 300/8



Order data

Order number	171000 300/8
GTIN	4045197439055
Item class	11R

Description

Version:

GARANT – saw blade made of molybdenum alloyed high performance cutting steel **HSS (DMo5)**. Due to constantly high hardness and extreme toughness, particularly **high cutting performances** are obtained (reduced cutting times and longer tool life). The precise set ensures a straight cut.

Tooth type: normal

Width: 25 mm

Thickness: 1.6 mm

Clamping hole Ø: 8.5 mm

Technical description

Length L	300 mm
Thickness	1.6 mm
Width	25 mm
TPI	8
Clamping hole Ø	8.5 mm
Tooth type	normal
Tool material	HSS
Type of product	Power saw blade

User data

	Suitability	V_c	ISO code
Aluminium (short chipping)	suitable only under restricted conditions		
Alu > 10% Si	suitable only under restricted conditions		
Steel < 500 N/mm ²	suitable		
Steel < 750 N/mm ²	suitable		
Steel < 900 N/mm ²	suitable only under restricted conditions		
wet maximum	suitable		