



Workshop compressor, Type: 300/30W



Order data

Order number	079841 300/30W
GTIN	2050001676559
Item class	03R

Description

Version:

Corrosion-free valves, highly efficient cooling, maintenance-free transmission components, corrosion-protected reservoir, minimum 10-year spare parts availability guarantee. High efficiency for low operating costs. "On-site compressor", with all-round steel frame protection, for small to medium air requirements.

Supplied with:

Filter pressure regulator with manometer, quick-release connection.

Note:

Other workshop compressors available on request.

Technical description

Power consumption	1.5 kW
maximum filling rate	215 l/min
Weight	43 kg
Manufacturer's designation	300/30W
Length	770 mm
Pressure vessel volume	30 l
maximum suction rate	300 l/min

Width	510 mm
Height	450 mm
maximum pressure (air)	10 bar
Type of product	Compressor