

**Filters 5 µm, Internal thread Ø: 1/2in****Order data**

Order number	080014 1/2
GTIN	4047322129367
Item class	08A

**Description****Version:**

Service units can be made up as required; the connection clip supplied can be used to add extensions.

**Service unit** in modular series ("multifix" system), consisting of filter, pressure regulator and mist atomiser. Control range 0.5- 10 bar, operating pressure maximum 16 bar, operating temperature maximum 60 °C.

**Advantage:**

The service unit can be configured individually, e. g. with several pressure regulators, without oil atomiser (for oil-free tools) etc.

**Application:**

For systems in the pressure range up to 16 bar. Compatible with the products of CEJN, RECTUS and JWL.

**Technical description**

Internal thread Ø	1/2 in
Overall length (L) as 3-part service unit	202 mm
Flow rate for 3-part service unit	3100 l/min

Height (H)	248 mm
Type of product	Filter

---

## Accessories

Polycarbonate containerfor filter Glass Ø 53 mm	080024 53
---	-----------