

Garant

Power saw blade, HSS, Length L / TPI: 500/10



Order data

| | |
|--------------|---------------|
| Order number | 171000 500/10 |
| GTIN | 4045197094995 |
| Item class | 11R |

Description

Version:

GARANT – saw blade made of molybdenum alloyed high performance cutting steel **HSS (DMo5)**. Due to constantly high hardness and extreme toughness, particularly **high cutting performances** are obtained (reduced cutting times and longer tool life). The precise set ensures a straight cut.

Tooth type: normal

Width: 38 mm

Thickness: 2 mm

Clamping hole Ø: 10.5 mm

Technical description

| | |
|-----------------|-----------------|
| Width | 38 mm |
| Thickness | 2 mm |
| Length L | 500 mm |
| TPI | 10 |
| Clamping hole Ø | 10.5 mm |
| Tooth type | normal |
| Tool material | HSS |
| Type of product | Power saw blade |

User data

| | Suitability | V_c | ISO code |
|-------------------------------|---|----------------------|-----------------|
| Aluminium (short chipping) | suitable only under restricted conditions | | |
| Alu > 10% Si | suitable only under restricted conditions | | |
| Steel < 500 N/mm ² | suitable | | |
| Steel < 750 N/mm ² | suitable | | |
| Steel < 900 N/mm ² | suitable only under restricted conditions | | |
| wet maximum | suitable | | |