

## Flat magnet without thread, Ferrite, Ø: 63mm



### Order data

Order number	085910 63
GTIN	2050000965081
Item class	08Q

### Description

#### Version:

Shielded flat magnets with magnetic core made of **hard ferrite**.

- **Galvanised surface.**
- **Temperature-resistant up to maximum 120 °C.**

#### Application:

For clamping, assembling, incorporation by pressing in / gluing and fixing / holding.

### Technical description

Height	14 mm
Ø	63 mm
Nominal clamping force	350 N
Weight	230 g
maximum temperature resistance	120 °C
Material of the magnet core	Ferrite
Type of product	Flat gripper magnet