



Power saw blade, bimetal, Length L / TPI: 600/4



Order data

Order number	171100 600/4
GTIN	7311518114572
Item class	16D

Description

Version:

BAHCO bi-metal – a strip of HSS teeth welded to a flexible blade body of special steel using electron beam welding in a vacuum. In this way the saw blades are extremely hard at the tooth tips, but have **enormous flexibility** and are unbreakable even **at high feed rates**.

Tooth type: normal

Width: 50 mm

Thickness: 2.5 mm

Clamping hole Ø: 12.5 mm

Technical description

Length L	600 mm
Width	50 mm
TPI	4
Clamping hole Ø	12.5 mm
Thickness	2.5 mm
Tooth type	normal
Tool material	bimetal
Type of product	Power saw blade

User data

	Suitability	V _c	ISO code
--	-------------	----------------	----------

Aluminium (short chipping)	suitable only under restricted conditions
Alu > 10% Si	suitable only under restricted conditions
Steel < 500 N/mm ²	suitable
Steel < 750 N/mm ²	suitable
Steel < 900 N/mm ²	suitable
Steel < 1100 N/mm ²	suitable
Steel < 1400 N/mm ²	suitable only under restricted conditions
INOX < 900 N/mm ²	suitable only under restricted conditions
GG(G)	suitable
CuZn	suitable
Uni	suitable
wet maximum	suitable