

**Garant****Power saw blade, HSS, Length L / TPI: 450/8****Order data**

|              |               |
|--------------|---------------|
| Order number | 171000 450/8  |
| GTIN         | 4045197094940 |
| Item class   | 11R           |

**Description****Version:**

**GARANT** – saw blade made of molybdenum alloyed high performance cutting steel **HSS (DMo5)**. Due to constantly high hardness and extreme toughness, particularly **high cutting performances** are obtained (reduced cutting times and longer tool life). The precise set ensures a straight cut.

Tooth type: normal

Width: 32 mm

Thickness: 2 mm

Clamping hole Ø: 10.5 mm

**Technical description**

|                 |                 |
|-----------------|-----------------|
| Width           | 32 mm           |
| Length L        | 450 mm          |
| Thickness       | 2 mm            |
| Clamping hole Ø | 10.5 mm         |
| TPI             | 8               |
| Tooth type      | normal          |
| Tool material   | HSS             |
| Type of product | Power saw blade |

**User data**

|                               | <b>Suitability</b>                        | <b>V<sub>c</sub></b> | <b>ISO code</b> |
|-------------------------------|---|----------------------|-----------------|
| Aluminium (short chipping)    | suitable only under restricted conditions |                      |                 |
| Alu > 10% Si                  | suitable only under restricted conditions |                      |                 |
| Steel < 500 N/mm <sup>2</sup> | suitable                                  |                      |                 |
| Steel < 750 N/mm <sup>2</sup> | suitable                                  |                      |                 |
| Steel < 900 N/mm <sup>2</sup> | suitable only under restricted conditions |                      |                 |
| wet maximum                   | suitable                                  |                      |                 |