



## Precision cylinder lock with high shackle individual keys, Body Ø: 40mm



### Order data

Order number	085875 40
GTIN	4003482032602
Item class	08Q

### Description

#### Version:

Solid brass body, rust-free precision lock mechanism, steel shackle hardened and chrome-plated, double locked.

With extra high shackle.

The 116 Profi range is available on request in the following special versions: Locks according to a sample pattern or locking, with master key system and additional keys.

#### Function:

**Individual keys** means each key can open and close only **one** lock or cylinder, i.e. the key is unique.

#### Supplied with:

Padlock with 2 keys.

### Technical description

Hoop Ø	6 mm
Shackle, double lever mechanism	yes
Internal height of shackle	60 mm

tall shackle	yes
Material of the housing	Brass
Body Ø	40 mm
compatible with integrated locking systems	no
Number of keys	2
Material of the band	Chrome-plated steel
Hoop hardened	yes
Lock mechanism	rust-free precision lock mechanism
suitable for lock barrels	no
with keyhole cover	no
Number of locks	1
Locking	individual keys
Series	116 Profi
Type of product	Padlock