

**Garant**
**Power saw blade, HSS, Length L / TPI: 450/10**

**Order data**

|              |               |
|--------------|---------------|
| Order number | 171000 450/10 |
| GTIN         | 4045197094957 |
| Item class   | 11R           |

**Description**
**Version:**

**GARANT** – saw blade made of molybdenum alloyed high performance cutting steel **HSS (DMo5)**. Due to constantly high hardness and extreme toughness, particularly **high cutting performances** are obtained (reduced cutting times and longer tool life). The precise set ensures a straight cut.

**Technical description**

|                 |                 |
|-----------------|-----------------|
| Clamping hole Ø | 10.5 mm         |
| Width           | 32 mm           |
| Thickness       | 2 mm            |
| TPI             | 10              |
| Length L        | 450 mm          |
| Tooth type      | normal          |
| Tool material   | HSS             |
| Type of product | Power saw blade |

**User data**

|                            | Suitability                               | V <sub>c</sub> | ISO code |
|----------------------------|-------------------------------------------|----------------|----------|
| Aluminium (short chipping) | suitable only under restricted conditions |                |          |

|                               |                                           |
|-------------------------------|-------------------------------------------|
| Alu > 10% Si                  | suitable only under restricted conditions |
| Steel < 500 N/mm <sup>2</sup> | suitable                                  |
| Steel < 750 N/mm <sup>2</sup> | suitable                                  |
| Steel < 900 N/mm <sup>2</sup> | suitable only under restricted conditions |
| wet maximum                   | suitable                                  |