

**Garant****Power saw blade for Kasto, HSS, Length L / TPI: 350/6****Order data**

Order number	171150 350/6
GTIN	4045197095145
Item class	11R

**Description****Version:**

**GARANT** – saw blade made of molybdenum alloyed high performance cutting steel **HSS (DMo5)**. Due to constantly high hardness and extreme toughness, particularly **high cutting performances** are obtained (reduced cutting times and longer tool life). The precise set ensures a straight cut.

**Note:**

**Especially for Kasto machines** (clamping holes offset from 38 mm blade width).

**Important:** The instructions included with the saw blades must be followed in all details.

Tooth type: normal

Width: 32 mm

Thickness: 2 mm

Clamping hole Ø: 8.5 mm

**Technical description**

Width	32 mm
Thickness	2 mm
Clamping hole Ø	8.5 mm
TPI	6
Length L	350 mm
Tooth type	normal
Tool material	HSS
Type of product	Power saw blade

**User data**

	<b>Suitability</b>	<b>V<sub>c</sub></b>	<b>ISO code</b>
Aluminium (short chipping)	suitable only under restricted conditions		
Alu > 10% Si	suitable only under restricted conditions		
Steel < 500 N/mm <sup>2</sup>	suitable		
Steel < 750 N/mm <sup>2</sup>	suitable		
Steel < 900 N/mm <sup>2</sup>	suitable only under restricted conditions		
wet maximum	suitable		