



Workshop compressor, Type: 450/90D



Order data

Order number	079841 450/90D
GTIN	2050001676566
Item class	03R

Description

Version:

Corrosion-free valves, highly efficient cooling, maintenance-free transmission components, corrosion-protected reservoir, minimum 10-year spare parts availability guarantee. High efficiency for low operating costs. 2-cylinder compressor for medium air requirements, very easy to handle.

Supplied with:

Filter pressure regulator with manometer, quick-release connection.

Note:

Other workshop compressors available on request.

Technical description

Width	500 mm
Manufacturer's designation	450/90D
Length	1190 mm
Power consumption	2.4 kW
Weight	86 kg
maximum filling rate	330 l/min

Height	840 mm
maximum pressure (air)	10 bar
maximum suction rate	450 l/min
Pressure vessel volume	90 l
Type of product	Compressor