

## Flat magnet with internal thread, Ferrite, Ø: 32mm



### Order data

Order number	085915 32
GTIN	2050000965289
Item class	08Q

### Description

#### Version:

- **Shielded flat magnet made of hard ferrite with insert nut.**
- **Galvanised surface.**
- **Temperature-resistant up to maximum 120 °C.**

#### Application:

For clamping, assembling, incorporation by screw fastening.

#### Note:

Screw-in hooks with external thread under No. 085921.

### Technical description

Nominal clamping force	80 N
maximum temperature resistance	120 °C
Weight	32 g
Thread	M4 mm
Ø	32 mm
Height with thread	15 mm
Height	7 mm
Threaded socket	yes
Material of the surface	galvanised

Material of the magnet core	Ferrite
Type of product	Flat gripper magnet

---

## Accessories

Screw-in hook set with external thread 10 pieces Thread M4	085921 M4
--	-----------