

Flat magnet without thread, Ferrite, Ø: 80mm



Order data

Order number	085910 80
GTIN	2050000965098
Item class	08Q

Description

Version:

Shielded flat magnets with magnetic core made of **hard ferrite**.

- **Galvanised surface.**
- **Temperature-resistant up to maximum 120 °C.**

Application:

For clamping, assembling, incorporation by pressing in / gluing and fixing / holding.

Technical description

maximum temperature resistance	120 °C
Height	18 mm
Weight	485 g
Nominal clamping force	600 N
Ø	80 mm
Material of the magnet core	Ferrite
Type of product	Flat gripper magnet