



Pneumatic chisel hammer, Type: P2531-H



Order data

Order number	079730 P2531-H
GTIN	7322590059514
Item class	03R

Description

Version:

Handy **chisel hammer** for chiselling and separating.

Supplied with:

Including the necessary coupling adaptors.

Spare part:

Selected service kits: Sets of replacement parts for most Atlas Copco pneumatic tools can be supplied on request for preventive maintenance and servicing.

Technical description

recommended hose size (internal Ø)	10 mm
Tool arbor size	10.2 mm
Length	193 mm
Weight	1.5 kg
maximum vibration to EN	11.5 m/s ²
maximum air consumption	402 l/min

Manufacturer's designation	P2531-H
Tool arbor shape	Hexagon
Impact frequency	50 Hz
Operating noise	100 dB(A)
Compressed air connection	1/4 in
Connection thread	BSP
Type of product	Chisel mallet

Accessories

Chisel Dimensions 20X178 mm	079739 20X178
Chisel Dimensions 3,2X178 mm	079739 3,2X178