



Dynafile® pneumatic belt linisher, Type: 14010



Order data

Order number	079551 14010
GTIN	616026140103
Item class	03R

Description

Version:

Versatile machines with **adjustable linishing belt guides, exactly true-running belts**, and with an exchangeable **contact arm** allowing the use of contact wheel or side face. The composite linishing belt coating enables **quick** and **easy change of the linishing belt**. The **linishing belt** cooling via the exhaust air prolongs the working life of the belts. Adjustable handle **Dynafile®**, sturdy general-purpose linishing machine.

Application:

For abrading, deburring, blending, finishing and polishing, ideal also for flexible access to difficult places.

Supplied with:

Including the necessary coupling adaptors. **Dynafile®**, 5 contact arms, surface preparation set, linishing belt dimensions 3 – 4, 6, 13x610mm, transport case.

Note:

Other contact arm versions for Dynafile® from No. 079559 available on request or in our eShop.

Technical description

maximum vibration to EN	< 2.5 m/s ²
Tape width	3–4; 6; 13 mm
Operating noise	77 dB(A)

maximum speed	20000 min ⁻¹
Manufacturer's designation	Dynaflex I kit
Weight	1.4 kg
maximum air consumption	876 l/min
Band length	610 mm
Model range	Dynaflex
Output power	379 W
Compressed air connection	1/4 in
Connection thread	NPT
Packaging	Carrying case
Type of product	Finishing machine

Accessories

Contact arm for Dynaflex® Type 11216	079559 11216
Contact arm for Dynaflex® Type 11232	079559 11232
Contact arm for Dynaflex® Type 11218	079559 11218
Contact arm for Dynaflex® Type 11219	079559 11219
Contact arm for Dynaflex® Type 11213	079559 11213
Contact arm for Dynaflex® Type 11231	079559 11231